

# 19" Basic Wallmount Cabinet

6U, 400 mm Deep, IP20-Rated Housing, Flatpacked, Gray

Part No.: **714150**

---

## Features:

- High-quality basic wallmount
- Ideal for 19" rackmount applications
- Protection grade: IP20
- Maximum static load of 50 kg
- Reversible Front door
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Ships flatpacked
- Three-Year Warranty

## Specifications:

### General

- 19 in.
- Height: 6U
- Color: Gray RAL7035
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

### Dimensions

- 400 (L) x 540 (W) x 353 (H) [mm]
- 15.75 (L) x 21.26 (W) x 13.9 (H) [in]

### Package Contents

- Flat Pack Wallmount
- Installation Instructions

