

19" Basic Wallmount Cabinet

9U, 560 mm Deep, IP20-Rated Housing, Flatpacked, Gray

Part No.: **714815**

Features:

- High-quality basic wallmount
- Ideal for 19" rackmount applications
- Protection grade: IP20
- Maximum static load of 50 kg
- Reversible Front door
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Ships flatpacked
- Three-Year Warranty

Specifications:

General

- 19 in.
- Height: 9U
- Color: Gray RAL7035
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 560 (L) x 540 (W) x 487 (H) [mm]
- 22.05 (L) x 21.26 (W) x 19.17 (H) [in]

Package Contents

- Flat Pack Wallmount
- Installation Instructions

