




Date	SYM	REVISION RECORD	AUTH	DR.	CK.
10/24/14	E	REDRAWN AND UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
04/21/17	F	DIM. 57.70 WAS 58.40 DIM. 150.0 WAS 152.4 UPDATED NOTES	T.B.	B.S.	



NOTES:

- Plastic material - Polypropylene, PP-1040
- Flammability Rating -UL94-HB, UL File NO. E216959
- Temperature Range: -10°C to +100°C
- Springs - Nickel Plated Spring Steel
- Rivets - Brass, Nickel Plated
- Wire: 26AWG, UL1007, CSA, TR64, 300V, 80°C
- Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000
- ROHS 2 COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)		Scale	Drawn By B.S.
Fractional ± .8 (.030)	Title TWO "AA" CELL HOLDER WITH WIRE LEADS		
Angular ± 3°	Date 04/21/17	Drawing Number BC22AAW	
		Approved By T.B.	