



Fuse-Link:
5 x 20 mm
Mounting:
P.C.B.
Rated Current:
10 A
Rated Voltage:
250 V AC
Rated Power Acceptance:
4 W



Standard package:
1.000 pcs. Bulk

Housing:
High Temperature Thermoplastics UL 94V-0
Solderability:
Reflow – 245 °C / 30 sec. Max. acc. To J-STD-020-D
Admissible ambient air temperature:
-30 °C to 85 °C
Shocksafe category:
PC1
Degree of protection:
IP00 / IP20
Contact Resistance:
< 5mΩ
Standard colour:
Black



EN 60127-6

Rated Current
10 A
Rated Voltage
250 V AC
Rated Power Acceptance
4 W



UL 4248-1 + C22.2 no 4248-1

Rated Current
20 A
Rated Voltage
250 V AC

