

wowpen^{II} JOY

SIX

Programmable Buttons

Wireless



Multiple OS Supported

VERTICAL
Ergonomic Design

ilg
MADE IN CHINA
BY ILG, INC

A Revolution in PC & Mobile Input Devices



6 Programmable Buttons



Adjustable DPI Button
800 | 1200 | 2000 CPI

5,000,000 Hits
Life Time
Micro Switch



300,000 Loops
Life Time Encode



UV Elastic
Paint
+
Matte Paint

Front & Back
Button



Maximum Reception
Range **15M**



PIX4202
3 In 1 Sensor



Micro-B USB Charging Port



Lithium Polymer Battery
Can Keep **80%** Charge Quantity
After **300** charging

Hidden Wireless Receiver



SPECIFICATIONS (Wireless)

Micro switch : 5,000,000 hits life time(left and right)
Encode : 300,000 loops life time
Sensor : PIX4202 3 in 1 sensor
CPI : 800 - 1200 - 2000
Frame Rate : 2400 fps
Tracking speed : 30 ips
Acceleration : 10g
Run mode current : High speed 1.8mA/Low speed 1.6mA
Sleep mode current : 35uA
Battery : 430mah lithium polymer battery(with protective circuit)
Charging cable*1
Low voltage indication LED
Charging indication LED
Button : 6pcs(left/middle/right/cpi/front/back)
Interface : USB
Weight : 116g(with lithium polymer battery ; without packing)
Dimension : 100.5*81*80.3mm