



Vertical Rackmount 24-Output Power Distribution Unit (PDU)

20 x C13 & 4 x Output C19, Removable Power Cable, Rear C14 Input

Part No.: **163675**

Our new, 19" rackmountable PDU range displays Intellinet innovation and practicality. This comprehensive line offers a wide selection of tools to protect your valuable I.T. equipment. An integrated, removable cable plugs conveniently into the rear C14 input of the unit.

Features:

- Vertical rackmountable Power Distribution Unit
- Socket outlet Standard IEC320 C13 (x 20) & IEC320 C19 (x 4)
- Socket input Standard IEC320 C14
- Cable specification: standard 2 m (6.6 ft.) removable power cord
- Three-Year Warranty

Specifications:

General

- Vertical Rackmount (recommended for cabinets 32U and above)
- Socket/outlet standard: IEC320 C13 (x 20) & IEC320 C19 (x 4)
- Outlets: 24
- Cable specification: standard 2 m (6.6 ft.) removable power cord
- Size: 1133.6 (L) x 45 (W) x 45 (H) [mm] / 44.63 (L) x 1.77 (W) x 1.77 (H) [in]
- Electrical rating: 110 - 250V AC
- Maximum load current: 16 A (IEC EU 10 A, North America 15 A)

Package Contents

- Vertical Rackmount 24-Output Power Distribution Unit (PDU)
- 2 m (6.6 ft.) power cord
- Two M6*12 screws
- Two M6 nuts
- Two plastic washers



C13 Output



C19 Output

