



4100mAh(typ)  
High capacity battery

Snapdragon 625  
14nm LPP FinFET

Metal body  
Front 2.5D curved glass

5.5"  
Full HD display

Colours



Black

Gold

Dark grey

## Processor & Memory

### 3GB + 32GB

Snapdragon 625, octa-core 2.0GHz

3GB LPDDR3

32GB eMMC 5.0 Flash

4G dual SIM

Up to 128GB expandable storage

### 4GB + 64GB

Snapdragon 625, octa-core 2.0GHz

4GB LPDDR3

64GB eMMC 5.0 flash

4G dual SIM

## Dimensions

# Redmi Note 4

Thickness: 8.45mm

Weight 165g

---

## Battery

4100mAh (typ) / 4000mAh (min) lithium-ion polymer battery

Non-removable

5V/2A charging

---

## Camera

### 13MP CMOS camera

Backside illumination (BSI) technology

1.12µm pixels

Ultra-fast 0.1s PDAF technology

### 5MP front camera

f/2.0 aperture

Smart and Pro Beautify

Face recognition

1080p full HD video recording

---

## Redmi Note 4

[Overview](#)[Design](#)[Camera](#)

1920 x 1080 resolution

1000:1 contrast ratio

72% NTSC color gamut

Night display

Reading mode

Colour temperature adjustment

---

## Connectivity

### Network bands:

4G	FDD-LTE	B1, B3, B4, B5, B7, B8, B20
	TDD-LTE	B38, B40
3G	WCDMA	B1, B2, B5, B8
2G	GSM	B2, B3, B5, B8

### 4G dual SIM:

3-choose-2 hybrid SIM tray

Nano-SIM + micro-SIM or Micro-SIM + micro SD card

### Dual SIM use:

When two SIM cards are used simultaneously, the primary SIM can support

4G+/ 4G / 3G / 2G calls and data while the secondary SIM can support 3G calls

only.

- Bluetooth 4.1
- Bluetooth HID
- Wi-Fi Display
- Wi-Fi Direct

---

## Buttons

## Redmi Note 4

[Overview](#) [Design](#) [Camera](#)

---

## Sensors

- Electronic compass
  - Accelerometer
  - Proximity sensor
  - Infrared
  - Ambient light sensor
  - Gyroscope
  - Hall sensor
- 

## GPS navigation

- GPS
  - AGPS
  - GLONASS
  - BeiDou positioning
- 

## Multimedia support

- MP4
- M4V
- MKV
- XVID
- AAC
- AAC+
- eAAC+
- MP3
- AMR
- FLAC

Supports H.265, H.264, H.263, MPEG4

---

## SAR information

- SAR 1g limit: 1.6W/kg
  - SAR Value: 0.375W/Kg (Max 15mm distance)
- 

## Package contents

Redmi Note 4 / Power adapter / USB 2.0 cable / Warranty card / User guide / SIM insertion tool

# Redmi Note 4

Only certain carrier data plans support VoLTE. Contact your carrier for more information.



**1 Year Limited  
Warranty For Phones**



**6 Month Limited  
Warranty For Accessories**

## LET'S STAY IN TOUCH

Get updates on sales specials and more

## FOLLOW MI

We want to hear from you!



### SHOP AND LEARN

[Mi Max / Mi 5](#)

[Redmi Note 3](#)

[Mi Power Bank](#)

### SUPPORT

[Warranty](#)

[Store Locator](#)

### ABOUT US

[Xiaomi](#)

[Privacy Policy](#)

### CONTACT US

[Facebook](#)

[MIUI Forum](#)

[Contact Us](#)