

Product information

00 21 19 LB E

KNIPEX L-BOXX® Electric

63 parts



- Equipped with 14 KNIPEX tools, a total of 63 brand tools, partly VDE-tested according to DIN EN 60900
- With a total of 48 inserting options
- Max. payload: 25 kg
- Strong box made of impact- and shock-proof ABS plastic
- Splash-proof
- Several boxes can be securely joined together
- Flexible inner partitions
- Handle can be lowered into a hollow in the lid to save space
- Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- With two-piece tool board made from dirt-repellent PP twin-wall sheets
- Tool boards are connected to each other using hook-and-loop
- Top section with 10 pockets and 10 elastic straps
- Top of base part with 7 pockets and strap for hanging up the tool board; can also be used to lift or lay the KNIPEX L-BOXX® down
- Bottom of base part with 7 pockets and 7 elastic straps
- Dimensions, exterior (W x H x D): 442 x 357 x 151 mm; dimensions, interior (W x H x D): 375 x 107 x 311 mm

General

Article No.	00 21 19 LB E
EAN	4003773081623
Weight	7,495 g
Dimensions	357 x 360 x 151 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	442 mm (375 mm)
Dimension exterior (interior) height mm	151 mm (107 mm)
Dimension exterior (interior) depth mm	357 mm

Content

08 26 145	1 x Needle-Nose Combination Pliers (145 mm) ⚡ 1000V  
12 52 195 SB	1 x KNIPEX PreciStrip16® Automatic Insulation Stripper (0,08 - 16 mm²)
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm²) ⚡ 1000V  
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) 
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool (180 mm) 
97 53 04	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 10 + 16 mm²) 

Content

98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (0,6 x 3,5 x 100 mm) ⚠ 1000V 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ1 x 80 mm) ⚠ 1000V 
98 52	1 x Cable Knife (190 mm) ⚠ 1000V
00 11 01	1 x Knipex KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems (92 mm)
26 26 200	1 x Knipex Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm) ⚠ 1000V   40° 
70 06 160	1 x Knipex Diagonal Cutter (160 mm) ⚠ 1000V 
74 06 200	1 x Knipex High Leverage Diagonal Cutter (200 mm) ⚠ 1000V 
87 01 180	1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (180 mm) 
101-0300	1 x Picard Locksmith's hammer (300 g)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
16135	1 x Stabila Spirit Level Type 70 Electric (430 mm)
18115	1 x Stabila Pocket Electric mini spirit level (68 mm)
003760	1 x Wera Joker open-end wrench (10 x 13 mm)
004018	1 x Wera 8100 SA 8 Zyklus set of metal ratchets 28 parts (1/4")
5003484001	1 x Wera VDE interchangeable blades, 16 parts, slim

Accessories

00 21 19 LB	KNIPEX L-BOXX® empty,
00 21 19 LB WK	Tool board for KNIPEX L-BOXX®,
00 21 19 LB LE	KNIPEX L-BOXX®, empty,

technical change and errors excepted

L-BOXX® is a registered trademark of Sortimo International GmbH