

Product information

00 21 41

Tool Case "BIG Twin Move" Electric

63 parts



- Equipped with 14 KNIPEX tools, a total of 63 brand tools, partly VDE-tested according to DIN EN 60900
- With a total of 95 inserting options
- Max. payload: 30 kg
- Volume: 38 litres
- Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 13 tool pockets
- Free-standing in all opening positions thanks to snap-in cover holders with hinge mechanism on both sides, angle freely adjustable
- Removable document compartment and removable tool boards made from dirt-repellent PP twin-wall sheets with 13 tool pockets
- Label field with two stickers for individual labelling
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Heavy duty ABS material, black
- Circumferential aluminium frame with securely mounted, sturdy centre wall that can be fitted on both sides, with versatile inserting options due to elasticated loops and twelve small pockets
- Metal hinges
- Three-digit combination lock for secure locking of the case
- Two metal tilt locks each for fixing the cover and the base
- Can be opened from one or both sides; bottom and lid can be opened independently of each other



General

Article No.	00 21 41
EAN	4003773082118
Weight	12,960 g
Dimensions	290 x 277 x 437 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	520 mm (490 mm)
Dimension exterior (interior) height mm	435 mm (370 mm)
Dimension exterior (interior) depth mm	290 mm (110 mm)

Content

08 26 145	1 x Needle-Nose Combination Pliers (145 mm) ⚠ 1000V  
12 52 195 SB	1 x KNIPEX PreciStrip16® Automatic Insulation Stripper (0,08 - 16 mm ²)
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm ²) ⚠ 1000V  
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) 
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool (180 mm) 
97 53 04	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 10 + 16 mm ²) 

Content

98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (0,6 x 3,5 x 100 mm) ⚠ 1000V 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ1 x 80 mm) ⚠ 1000V 
98 52	1 x Cable Knife (190 mm) ⚠ 1000V
00 11 01	1 x Knipex KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems (92 mm)
26 26 200	1 x Knipex Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm) ⚠ 1000V   40° 
70 06 160	1 x Knipex Diagonal Cutter (160 mm) ⚠ 1000V 
74 06 200	1 x Knipex High Leverage Diagonal Cutter (200 mm) ⚠ 1000V 
87 01 180	1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (180 mm) 
0030312-0300	1 x Picard Locksmith's hammer (300 g)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
16135	1 x Stabila Spirit Level Type 70 Electric (430 mm)
18115	1 x Stabila Pocket Electric mini spirit level (68 mm)
003760	1 x Wera Joker open-end wrench (10 x 13 mm)
004018	1 x Wera 8100 SA 8 Zyklus set of metal ratchets 28 parts (1/4")
5003484001	1 x Wera VDE interchangeable blades, 16 parts, slim

Accessories

00 21 41 LE	Tool Case "BIG Twin Move" empty,
-------------	----------------------------------

technical change and errors excepted