

Product information

98 20 35 SL

Screwdriver (Slim) for slotted screws

IEC 60900 DIN EN 60900

- Reduced extra slim shaft in the front area for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling



⚡ 1000 V 

General

Article No.	98 20 35 SL
EAN	4003773079712
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	35 g
Dimensions	202 x 25 x 23 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Blade length	100 mm
Length of non-insulated blade	15 mm
Handle length	102 mm
Blade width	3.5 mm
Blade thickness	0.6 mm
VDE tested	yes

technical change and errors excepted