

## Product information

# 98 25 02 SLS

## Screwdriver (Slim) Plus/Minus

Pozidriv®

IEC 60900 DIN EN 60900

- Driving tips for PlusMinus profile screws
- Use with electronics installation components, e.g. automatic circuit breakers
- Reduced extra slim shaft in the front area for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling



⚡ 1000V

| General         |                                               |
|-----------------|-----------------------------------------------|
| Article No.     | 98 25 02 SLS                                  |
| EAN             | 4003773081067                                 |
| point           | burnished                                     |
| Handles         | insulating multi-component handle, VDE-tested |
| Weight          | 89 g                                          |
| Dimensions      | 212 x 33 x 35 mm                              |
| Standard        | DIN EN 60900 IEC 60900                        |
| REACH compliant | does not contain SVHC                         |
| RoHS compliant  | not applicable                                |

| Technical details             |        |
|-------------------------------|--------|
| Size                          | PZ/S 2 |
| Blade length                  | 100 mm |
| Handle length                 | 118 mm |
| Length of non-insulated blade | 18 mm  |
| VDE tested                    | yes    |

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.

