

ORBIFOT

Description:

- Extremely robust photocell thanks to its special protection against electrical storms.
- Higher grade of protection IP 65 which allows it to work in extreme conditions. Simple N/O contact.
- Activation delay to avoid unwanted switch-on or switch-off due to vehicle headlights, clouds or other factors.
- Mounting: Threaded on luminaire or Surface with brackets.

Technical specifications:

Power supply voltage	120 or 230 V AC 50 - 60Hz
Switching capacity	10 A / 250 V AC <ul style="list-style-type: none"> • Incandescent: 800W • Fluorescent: N/A • Halogen 12 V ac: 600VA • Halogen 230 V ac: 800W • Low Consumption: N/A • LED: N/A
Max. Recomm. Load	
Operating temp	-10° C to +50° C
Sensivity	5 - 1000 Lux
Activation delay	25 Sec.
Protection degree	IP 65 according to EN 60529

