







REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE



More than 6P
the reinforcement



NOTES1:

UL Standard

1. Rated voltage/current : 150V / 5A
2. Withstanding voltage : AC1300V/1Min.

IEC Standard

1.

Pollution degree	2
Overtoltage category	II
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	100V
Rate current(A)	4A

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 2.5mm, Poles : N=04~24P
3. Operating temperature: -40°C~+105°C
4. Undimensioned tolerances:


Pitch range in mm	Nominal dimension range in mm				-	∩	□	
	Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100				Over 100 TO 150
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	0.1/10
							<	±2*

5. RoHS Compliance

15EDGRH - 2.5 - XXP - 1Y - 00A (H)

(Series No.) (Pitch) (Poles) (Color): 1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

(Single Pitch) (RoHS)
00A-(Standard)



DETACHED LISTS	PART NO.:	/			
	APPD:	/			
	CHKD:	/			
	DRFT:	/			
	THIRD ANGLE PROJECTION		DRAWING NO.:		MM (INCH)
		NAME:		DO NOT SCALE DRAWING	
		TITLE:		SCALE	
		CUSTOMER DRAWING		REV	
		NINGBO DEGSON ELECTRICAL CO., LTD		DO	
		15EDGRH-2.5-XXP-1Y-00A(H)		SHEET	
		1/1		1/1	