



NOTE:

1. Electrical test:

- (1). 100% open short & miss wire test;
- (2). Insulation resistance: DC 300V 10M ohm;
- (3). Contact resistance: 3 ohm;
- (4). Dielectric strength: 100V AC/Sec, 1mA.

2. RoHS 3.0 and REACH Compliant

3. MARKING: USB 3.1 CABLE E***** AWM STYLE 2725 80°C 30V VW-1

chart:

ITEM NO.	L±T (mm)
1620632	150±20
1620631	300±20
1460359	500±30
1460360	1000±30
1460361	1800±40

④	OUTER MOLD	PVC Black	2	
③	CONNECTOR	USB A/M SOLDER TYPE, BLUE INSULATION, THE PIN GOLD PLATED, THE SHELL FOR Nickel PLATED	1	
②	CONNECTOR	USB TYPE C/M SOLDER TYPE, BLACK INSULATION, THE PIN GOLD PLATED, THE SHELL FOR Nickel PLATED	1	
①	CABEL	[32AWG*1P+D+AL+MYLAR]*2PCS+24AWG*2C+32AWG*1P+AL+D+Braid AL-MG PVC/BLACK Jacket OD: 4.5±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK

Renkforce					
CUSTOMER	CN		BN.	See the chart	
PRODUCT NAME	USB 3.2 10Gbps 3A AM-CM Cable		UNIT	MM	
DRAWNBY	CHECKBY	APPOBY	DATE		
Alvan	Alvan		2021. 04. 26		

		NEW	2021. 04. 26	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.