Product Information Sheet EN

COMMISSION DELEGATED REGULATION (EU) 2019/2016

Supplier's name or trademark:	Amica			
Supplier's address:	Amica S.A. 64-510 Wronki, Mickiewicza 52, Poland			
Model identifier:	KGC15636P / VD 1442 AP			1171107
Type of refrigerating appliance:				
Low-noise appliance:	—	Design type:	Built-in	
			Free standing	√
Wine storage appliance:	—	Other refrigerating appliance:		√

General product parameters:

Parameter		Value	Parameter		Value
Overall dimensions (millimetre)	Height	1440	Total volume (dm³ or l)		206
	Width	550			
	Depth	615			
EEI		99,5	Energy efficiency class		E
Airborne acoustical noise emissions (dB(A) re 1 pW)		39	Airborne acoustical noise emission class		C
Annual energy consumption (kWh/a)		179,95	Climate class:	Extended Temperate	
				Temperate	
				Subtropical	√
				Tropical	
Minimum ambient temperature (ºC), for which the refrigerating appliance is suitable		16	Maximum ambient temperature (ºC), for which the refrigerating appliance is suitable		38
Winter setting		—			

Compartment Parameters:

Compartment type		Compartment parameters and values			
		Compartment volume (dm³ or l)	Recommended temperature setting for optimised food storage (ºC) These settings shall not contradict the storage conditions set out in Annex IV, Table 3	Freezing capacity (kg/24h)	Defrosting type (auto-defrost=A, manual defrost=M)
Pantry	—	—	—	—	—
Wine storage	—	—	—	—	—
Cellar	—	—	—	—	—
Fresh food	√	162	4	—	A
Chill	—	—	—	—	—
0-star or icemaking	—	—	—	—	—
1 -star	—	—	—	—	—
2 -star	—	—	—	—	—
3 -star	—	—	—	—	—
4 -star	√	44	-18	2	M
2-star section	—	—	—	—	—
Variable temperature compartment	—	—	—	—	—

For 4-star compartments			
Fast freeze facility	—		
Light source parameters:			
Type of light source	LED	√	
	Incandescent	—	
Energy efficiency class	F		
Minimum duration of the guarantee offered by the manufacturer (months):	12		
Additional information:			

Weblink to the manufacturer's website, where the information in point4(a) Annex of Commission Regulation (EU) 2019/2019 is found: http://www.amica-group.com/