

## Product Overview - 320-17IKB, 320-17ISK

---



320-17IKB (Type 80XM), 320-17IKB (Type 81BJ), 320-17ISK

### Features and specifications

Form Factor	<ul style="list-style-type: none"> <li>• Dimensions: Appr. 418 mm x 292.6 mm x 24.9 mm</li> <li>• Weight: Appr. 2.8 kg with battery</li> <li>• LCD size: 17.3-inch</li> </ul>
Processor	<ul style="list-style-type: none"> <li>• See the system properties of your computer. You can do this as follows: Click <b>Control Panel</b>, then click <b>Hardware and Sound</b>, click <b>Device Manager</b> under <b>Devices and Printers</b> and double click <b>Processors</b>.</li> </ul>
Memory	<ul style="list-style-type: none"> <li>• Type and speed: DDR4-2133 MHz</li> <li>• Maximum supported capacity: 16 GB</li> <li>• Slots: SODIMM x 1, on board x 1</li> </ul>
Hard disk drive	<ul style="list-style-type: none"> <li>• Form factor: 2.5-inch, 7 mm</li> <li>• Capacity: HDD: 500 GB/1 TB/2 TB SSD: 128 GB/256 GB/512 GB</li> <li>• Interface: SATA 3</li> </ul>
Optical Drive	<ul style="list-style-type: none"> <li>• Form factor: 9.0 mm</li> <li>• Type: Writer</li> </ul>
Display	<ul style="list-style-type: none"> <li>• Display resolution (LCD): 16:9 (1,600 x 900/1,920 x 1,080 pixels)</li> <li>• LCD backlight: LED</li> </ul>
I/O Ports	<ul style="list-style-type: none"> <li>• USB: USB 3.0 x 2, Type-C x 1</li> <li>• Audio: Combo audio jack x 1</li> <li>• Video/Audio: HDMI slot x 1</li> <li>• Ethernet: RJ-45 x 1</li> <li>• Memory card slot: 4 in 1 slot x 1 (SD/SDHC/SDXC/MMC)</li> </ul>
Battery pack	<ul style="list-style-type: none"> <li>• Type: Li-ion battery pack</li> <li>• Cells/Capacity: 2 cells, 30 Wh/35 Wh</li> <li>• <b>Note:</b> The capacity given here is the typical or average capacity as measured in a specific test environment. Capacities measured in other environments may differ but are no lower than the rated capacity (see product label).</li> </ul>
AC power adapter	<ul style="list-style-type: none"> <li>• Input: 100-240 V, 50-60 Hz</li> <li>• Output voltage: 20 V DC</li> <li>• Power: 45/65 W</li> </ul>
Miscellaneous	<ul style="list-style-type: none"> <li>• Camera: 0.3 M/HD</li> <li>• Security: Kensington mini security slot x 1</li> </ul>

## Manuals

**Hardware Maintenance Manual** (/docs/UM921045) - Information regarding hardware installation and removal, diagnostics, hardware interfaces, and replacement (FRU) part numbers.

**Note:** Specifications are dependent on the machine type and model.

- The capacity given here is the typical or average capacity as measured in a specific test environment. Capacities measured in other environments may differ but are no lower than the rated capacity (see product label).

**User Guide** (/docs/UM921049) - For further troubleshooting, performance and specification information, please see the User Guide.

**Note:** The features described in this guide are common to most models. Some features may not be available on your computer or your computer may include features that are not described in this User Guide.

PC-Support ▼	In PC-Support suchen	
--------------	----------------------	---