

HELUcond PP corrugated tubes, polypropylene

medium stress



HELUcond PP

Cable protection tube for medium stress applications.
Capacity/100mm NW 17: approx. 350 N

Application

- Plant and machine construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Chemical plants
- Heating and air-conditioning technology

Material

Polypropylene
UV-resistant

Flammability acc. to UL 94: HB

- halogen-free
- cadmium-free

Properties

resistant to a multitude of

- fuels
- mineral oils
- greases
- weak bases
- weak acids

Note

Suitable connection glands:
HELUquick, HSSV.

Technical data

Temperature range: -40°C up to +130°C
Temperature range temporary up to +150°C

fine profile

Part no. black	trade size mm	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
					up to 100	101 - 500	501 - 1000
920170	7,5	6,7	10,0	100	o. r.	o. r.	o. r.
920171	10,0	9,7	12,8	50	o. r.	o. r.	o. r.
920172	12,0	11,6	15,7	50	o. r.	o. r.	o. r.
920173	14,0	14,1	18,4	50	o. r.	o. r.	o. r.
920174	17,0	16,5	21,0	50	o. r.	o. r.	o. r.
920175	23,0	23,0	28,0	50	o. r.	o. r.	o. r.
920176	29,0	28,8	34,0	50	o. r.	o. r.	o. r.
920177	37,0	33,5	41,6	25	o. r.	o. r.	o. r.
920178	50,0	44,8	53,4	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request