

# HELUquick corrugated tubes conduit gland - straight

plastic male thread



## HELUquick gland straight

Quick-insert glands with metallic female thread for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

## Material

Polyamide PA 6

- halogen-free
- silicone-free
- cadmium-free

## Technical data

Protection class: IP 68

Temperature range: -40°C up to +115°C

## Properties

resistant to a multitude of

- oil
- gasoline
- weak bases
- weak acids

## Note

- UR-tested
- Disassembly without additional opener.  
Also available angled (45° and 90°).

## metric thread

Part no. grey	Part no. black	Size Metric	Suitable for ND	Thread length mm	Spanner size mm	Unit	Net EUR/ 100 items at a purchase of		
							up to 100	101 - 500	501 - 1000
904797	904820	M12 x 1,5	7,5	11,5	16,0	50	o. r.	o. r.	o. r.
904798	904821	M12 x 1,5	10,0	12,0	18,0	50	o. r.	o. r.	o. r.
904799	904822	M16 x 1,5	10,0	11,5	18,0	50	o. r.	o. r.	o. r.
904800	904823	M16 x 1,5	12,0	11,5	21,0	50	o. r.	o. r.	o. r.
904801	904824	M20 x 1,5	12,0	13,0	21,0	50	o. r.	o. r.	o. r.
904802	904825	M20 x 1,5	17,0	13,0	27,0	50	o. r.	o. r.	o. r.
904803	904826	M25 x 1,5	17,0	13,0	27,0	50	o. r.	o. r.	o. r.
904804	904827	M25 x 1,5	23,0	13,0	34,0	25	o. r.	o. r.	o. r.
904861	904828	M32 x 1,5	23,0	15,0	34,0	25	o. r.	o. r.	o. r.
904862	904829	M32 x 1,5	29,0	15,0	40,0	25	o. r.	o. r.	o. r.
904863	904830	M40 x 1,5	29,0	15,0	40,0	25	o. r.	o. r.	o. r.
904864	904831	M40 x 1,5	37,0	17,0	55,0	25	o. r.	o. r.	o. r.
904865	904832	M50 x 1,5	37,0	17,0	60,0	25	o. r.	o. r.	o. r.
904866	904833	M50 x 1,5	50,0	17,0	65,0	10	o. r.	o. r.	o. r.
904867	904834	M63 x 1,5	50,0	17,0	70,0	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request