

# HELUquick corrugated tubes conduit gland - elbow 90°

male thread, plastic



## HELUquick gland elbow 90°

Quick-insert glands for a reliable, quick connection.  
Suitable for parallel-coiled HELUcond protection tubes.

### Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction

### Material

Polyamide PA 6

- halogen-free
- silicone-free
- cadmium-free

### Properties

resistant to a multitude of

- oil
- gasoline
- weak bases
- weak acids

### Note

- UR-tested
- Disassembly without additional opener.  
Also available straight and angled 45°.

### Technical data

Protection class: IP 68

Temperature range: -40°C up to +115°C

### metric thread

Part no. grey	Part no. black	Size Metric	Suitable for ND	Thread length mm	Spanner size mm	Unit	Net EUR/ 100 items at a purchase of		
							up to 100	101 - 500	501 - 1000
904805	904835	M10 x 1,0	7,5	12,0	-	50	o. r.	o. r.	o. r.
904806	904836	M12 x 1,5	10,0	10,0	-	50	o. r.	o. r.	o. r.
904807	904837	M16 x 1,5	10,0	12,0	-	50	o. r.	o. r.	o. r.
904808	904838	M16 x 1,5	12,0	12,0	-	50	o. r.	o. r.	o. r.
904809	904839	M20 x 1,5	12,0	13,0	-	50	o. r.	o. r.	o. r.
904810	904840	M20 x 1,5	17,0	13,0	-	50	o. r.	o. r.	o. r.
904811	904841	M25 x 1,5	17,0	13,0	-	50	o. r.	o. r.	o. r.
904812	904842	M25 x 1,5	23,0	13,0	-	50	o. r.	o. r.	o. r.
904813	904843	M32 x 1,5	23,0	15,0	-	25	o. r.	o. r.	o. r.
904814	904844	M32 x 1,5	29,0	15,0	-	10	o. r.	o. r.	o. r.
904815	904845	M40 x 1,5	29,0	15,0	-	10	o. r.	o. r.	o. r.
904816	904846	M40 x 1,5	37,0	15,0	-	10	o. r.	o. r.	o. r.
904817	904847	M50 x 1,5	37,0	15,5	-	10	o. r.	o. r.	o. r.
904818	904848	M50 x 1,5	50,0	15,0	-	5	o. r.	o. r.	o. r.
904819	904849	M63 x 1,5	50,0	16,0	-	5	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request