

# HSSV corrugated tubes conduit gland - elbow 90°

metal male thread



## HSSV gland 90° with metallic male thread

Quick-insert glands with metallic male thread for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

### Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction

### Material

Polyamide PA 6

Flammability acc. to UL 94: VO

- halogen-free

### Properties

resistant to a multitude of

- fuels
- mineral oils
- greases
- weak bases
- weak acids

### Note

- UR-tested

Protection classification:

- IP 66 with outer seal

Threaded connection:

metric to EN 60423

Each unit includes 1 safety opener.

### Technical data

Protection class: IP 65

Temperature range: -40°C up to +110°C

### metric thread

Part no. grey	Part no. black	Size Metric	Suitable for ND	Thread length mm	Unit	Net EUR/100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
920247	920256	M12 x 1,5	10,0	10,0	50	o. r.	o. r.	o. r.
920248	920257	M16 x 1,5	10,0	10,5	50	o. r.	o. r.	o. r.
920249	920258	M16 x 1,5	12,0	10,5	50	o. r.	o. r.	o. r.
920250	920259	M20 x 1,5	17,0	12,0	50	o. r.	o. r.	o. r.
920251	920260	M25 x 1,5	21,0 / 23,0	15,0	50	o. r.	o. r.	o. r.
920252	920261	M32 x 1,5	29,0	15,0	25	o. r.	o. r.	o. r.
920253	920262	M40 x 1,5	36,0 / 37,0	16,0	25	o. r.	o. r.	o. r.
920254	920263	M50 x 1,5	48,0 / 50,0	16,0	10	o. r.	o. r.	o. r.
920255	920264	M63 x 1,5	48,0 / 50,0	16,0	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request