

HSSV-ZE corrugated tubes cable gland with strain relief

plastic male thread



Conduit gland HSSV with strain relief

Combined quick-insert cable glands for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction

Material

Polyamide PA 6

- halogen-free
- cadmium-free

Properties

resistant to a multitude of

- fuels
- mineral oils
- greases
- weak bases
- weak acids

Note

Threaded connection:
metric to EN 60423
Each unit includes 1 safety opener

Technical data

Protection class by tube: IP 65

Temperature range: -25°C up to +100°C

metric thread

Part no. grey	Part no. black	Size	Suitable for tube ND	Thread length mm	Unit	Net EUR/100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
903459	903466	M16 x 1,5	10,0	7,5	50	o. r.	o. r.	o. r.
903460	903467	M16 x 1,5	12,0	7,5	50	o. r.	o. r.	o. r.
903461	903468	M20 x 1,5	17,0	8,5	50	o. r.	o. r.	o. r.
903462	903469	M25 x 1,5	23,0	10,5	50	o. r.	o. r.	o. r.
903463	903470	M32 x 1,5	29,0	10,5	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request