

# COV corrugated tubes-conduit gland

dividable



## COV tube gland

Tube gland for HELUcond CO protection tubes. Axial fold-up and reclosable connection gland with shaped locking rods. Split nut with safety lock to prevent accidental opening.

## Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction

## Material

Polyamide PA 6

Flammability acc. to UL 94: HB

- halogen-free

## Properties

Resistant to a multitude of

- fuels
- mineral oils
- greases
- weak bases
- weak acids

## Technical data

Protection class: IP 43 ohne Dichtung

Temperature range: -40°C up to +125°C  
Temperature range temporary up to +150°C

## metric thread - dividable conduit gland

Part no. black	Size Metric	Suitable for ND	Thread length mm	Spanner size mm	Unit	Net EUR/ 100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
905031	M16 x 1,5	10,0	11,0	19,0	100	o. r.	o. r.	o. r.
905032	M20 x 1,5	14,0	11,0	27,0	100	o. r.	o. r.	o. r.
905033	M25 x 1,5	20,0	12,0	30,0	50	o. r.	o. r.	o. r.
905034	M32 x 1,5	23,0	15,0	36,0	50	o. r.	o. r.	o. r.
905035	M40 x 1,5	37,0	19,0	46,0	25	o. r.	o. r.	o. r.
905036	M50 x 1,5	45,0	19,0	55,0	25	o. r.	o. r.	o. r.

## metric thread - dividable counternut

Part no. black	Size Metric	Suitable for ND	Thread length mm	Spanner size mm	Unit	Net EUR/ 100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
905037	M16 x 1,5	10,0	8,0	19,0	100	o. r.	o. r.	o. r.
905038	M20 x 1,5	14,0	8,0	27,0	100	o. r.	o. r.	o. r.
905039	M25 x 1,5	20,0	9,0	30,0	50	o. r.	o. r.	o. r.
905040	M32 x 1,5	23,0	12,0	36,0	50	o. r.	o. r.	o. r.
905041	M40 x 1,5	37,0	15,0	46,0	25	o. r.	o. r.	o. r.
905042	M50 x 1,5	45,0	15,0	55,0	25	o. r.	o. r.	o. r.

## PG thread - dividable conduit gland wit counternut

Part no. black	Size PG	Suitable for ND	Thread length mm	Spanner size mm	Unit	Net EUR/ 100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
93514	9	10,0	12,0	22,0	100	o. r.	o. r.	o. r.
93515	13,5	14,0	17,0	30,0	100	o. r.	o. r.	o. r.
93516	21	20,0	17,0	36,0	50	o. r.	o. r.	o. r.
93517	29	23,0	21,0	46,0	50	o. r.	o. r.	o. r.
93518	29	37,0	22,0	55,0	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request