

SPR-PVC-AS metal cable tubes with plastic sheath

with latches profile



Type SPR-PVC-AS

Spiral wound metallic tube with latched profile and PVC sheath.

Weather-resistant, high tensile and transverse pressure load rating.

Application

- Plant and machine construction
- Automation technology
- Control cabinet construction

Material

Cold strip DC 03 acc. to EN10139, galvanised, Fe/Zn 3 or rustproof steel

Outer sheath material: PVC

Technical data

Temperature range: -25°C up to +80°C

Temperature range temporary up to +100°C

Note

Suitable connection glands:
US, LI

Part no. grey	Part no. black	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
					up to 100	101 - 500	501 - 1000
97032	97702	7,0	10,0	50	o. r.	o. r.	o. r.
97033	97685	10,0	14,0	50	o. r.	o. r.	o. r.
97034	97703	13,0	17,0	50	o. r.	o. r.	o. r.
97035	97704	15,0	19,0	50	o. r.	o. r.	o. r.
97036	97705	17,0	21,0	50	o. r.	o. r.	o. r.
97037	97706	22,0	27,0	50	o. r.	o. r.	o. r.
97038	97707	29,0	36,0	25	o. r.	o. r.	o. r.
97039	97708	38,0	45,0	25	o. r.	o. r.	o. r.
97040	97709	49,0	56,0	25	o. r.	o. r.	o. r.

small package

Part no. grey	Part no. black	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
					up to 100	101 - 500	501 - 1000
94890	94934	7,0	10,0	10	o. r.	o. r.	o. r.
94891	94935	10,0	14,0	10	o. r.	o. r.	o. r.
94892	94936	13,0	17,0	10	o. r.	o. r.	o. r.
94893	94937	15,0	19,0	10	o. r.	o. r.	o. r.
94894	94938	17,0	21,0	10	o. r.	o. r.	o. r.
94895	94939	22,0	27,0	10	o. r.	o. r.	o. r.
94896	94940	29,0	36,0	10	o. r.	o. r.	o. r.
94897	94941	38,0	45,0	10	o. r.	o. r.	o. r.
94898	94942	49,0	56,0	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request