

LK-I tube connectors, plastic

for flexible use



LK-I

Tube gland for protection tubes type S, S-PU and K.

Material

Polypropylene

Technical data

Protection class: IP 54

Temperature range: -10°C up to +110°C

Application

- Plant and machine construction
- Automation technology
- Installation technology
- Control cabinet construction

metric thread

Part no. grey	Size Metric	Tube outer Ø mm	Thread length mm	Unit	Net EUR/100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
97602	M12 x 1,5	10,0	10,0	50	o. r.	o. r.	o. r.
97603	M16 x 1,5	14,0	10,0	50	o. r.	o. r.	o. r.
97604	M20 x 1,5	17,0	10,0	50	o. r.	o. r.	o. r.
97605	M25 x 1,5	21,0	11,0	50	o. r.	o. r.	o. r.
97606	M32 x 1,5	27,0	12,0	25	o. r.	o. r.	o. r.
97607	M40 x 1,5	36,0	12,0	25	o. r.	o. r.	o. r.
97608	M50 x 1,5	45,0	12,0	25	o. r.	o. r.	o. r.
97609	M63 x 1,5	56,0	15,0	10	o. r.	o. r.	o. r.

metric thread - small packages

Part no. grey	Size Metric	Tube outer Ø mm	Thread length mm	Unit	Net EUR/100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
93480	M12 x 1,5	10,0	10,0	10	o. r.	o. r.	o. r.
93481	M16 x 1,5	14,0	10,0	10	o. r.	o. r.	o. r.
93482	M20 x 1,5	17,0	10,0	10	o. r.	o. r.	o. r.
93483	M25 x 1,5	21,0	11,0	10	o. r.	o. r.	o. r.
93484	M32 x 1,5	27,0	12,0	10	o. r.	o. r.	o. r.
93485	M40 x 1,5	36,0	12,0	2	o. r.	o. r.	o. r.
93486	M50 x 1,5	45,0	12,0	2	o. r.	o. r.	o. r.
93487	M63 x 1,5	56,0	15,0	2	o. r.	o. r.	o. r.

Continuation ►

LK-I tube connectors, plastic

for flexible use

PG thread

Part no. grey	Size PG	Tube outer Ø mm	Thread length mm	Unit	Net EUR/ 100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
90720	7	10,0	10,0	50	o. r.	o. r.	o. r.
90721	9	14,0	10,0	50	o. r.	o. r.	o. r.
90722	11	17,0	10,0	50	o. r.	o. r.	o. r.
90723	13,5	19,0	10,0	50	o. r.	o. r.	o. r.
90724	16	21,0	11,0	50	o. r.	o. r.	o. r.
90725	21	27,0	11,0	25	o. r.	o. r.	o. r.
90726	29	36,0	12,0	25	o. r.	o. r.	o. r.
90727	36	45,0	12,0	25	o. r.	o. r.	o. r.
90729	48	56,0	15,0	10	o. r.	o. r.	o. r.

PG thread - small packages

Part no. grey	Size PG	Tube outer Ø mm	Thread length mm	Unit	Net EUR/ 100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
93470	7	10,0	10,0	10	o. r.	o. r.	o. r.
93471	9	14,0	10,0	10	o. r.	o. r.	o. r.
93472	11	17,0	10,0	10	o. r.	o. r.	o. r.
93473	13,5	19,0	10,0	10	o. r.	o. r.	o. r.
93474	16	21,0	11,0	10	o. r.	o. r.	o. r.
93475	21	27,0	11,0	10	o. r.	o. r.	o. r.
93476	29	36,0	12,0	2	o. r.	o. r.	o. r.
93477	36	45,0	12,0	2	o. r.	o. r.	o. r.
93478	48	56,0	15,0	2	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request