

US tube gland brass nickel plated

with high degree of protection



US

Tube gland for protection tubes type S, S-PU, M, SPR-AS, SPR-PVC-AS, SPR-PU-AS, SPR-EDU-AS.

Application

- Plant and machine construction
- Automation technology
- Installation technology
- Control cabinet construction

Material

Brass, nickel plated
Grounding sleeve: Brass, bare
Seal: plastic

Technical data

Temperature range: -25°C up to +100°C

Note

Protection classification:
IP 65 - type: SPR-PVC-AS, SPR-PU-AS
IP 54 - type: S, S-PU
IP 40 - type: M, SPR-AS, SPR-EDU-AS

metric thread

Part no. S	Part no. M	Part no. SPR-AS	Part no. SPR-PVC-AS SPR-PU-AS	Part no. SPR-EDU-AS	Size	Tube outer Ø mm	Thread length mm	Unit	Net EUR/ 100 items at a purchase of		
									up to 100	101 - 500	501 - 1000
98331	98233	98241	98249	905989	M10 x 1,0	10,0	10,0	50	o. r.	o. r.	o. r.
98332	98234	98242	98250	905990	M12 x 1,5	14,0	10,0	50	o. r.	o. r.	o. r.
98333	98235	98243	98251	905991	M16 x 1,5	17,0	10,0	50	o. r.	o. r.	o. r.
98334	98236	98244	98252	905992	M20 x 1,5	21,0	10,0	50	o. r.	o. r.	o. r.
98335	98237	98245	98253	905993	M25 x 1,5	27,0	11,0	25	o. r.	o. r.	o. r.
98336	98238	98246	98254	905994	M32 x 1,5	36,0	13,0	25	o. r.	o. r.	o. r.
98337	98239	98247	98255	905995	M40 x 1,5	45,0	13,0	20	o. r.	o. r.	o. r.
98338	98240	98248	98256	905996	M50 x 1,5	56,0	14,0	10	o. r.	o. r.	o. r.

metric thread - small package

Part no. S	Part no. M	Part no. SPR-AS	Part no. SPR-PVC-AS SPR-PU-AS	Part no. SPR-EDU-AS	Size Metric	Tube outer Ø mm	Thread length mm	Unit	Net EUR/ 100 items at a purchase of		
									up to 100	101 - 500	501 - 1000
93530		93570	93590		M10 x 1,0	10,0	10,0	10	o. r.	o. r.	o. r.
93531		93571	93591		M12 x 1,5	14,0	10,0	10	o. r.	o. r.	o. r.
93532		93572	93592		M16 x 1,5	17,0	10,0	10	o. r.	o. r.	o. r.
93533		93573	93593		M20 x 1,5	21,0	10,0	10	o. r.	o. r.	o. r.
93534		93574	93594		M25 x 1,5	27,0	11,0	10	o. r.	o. r.	o. r.
93535		93575	93595		M32 x 1,5	36,0	13,0	2	o. r.	o. r.	o. r.
93536		93576	93596		M40 x 1,5	45,0	13,0	2	o. r.	o. r.	o. r.
93537		93577	93597		M50 x 1,5	56,0	14,0	2	o. r.	o. r.	o. r.

Continuation ►

US tube gland brass nickel plated

with high degree of protection

PG thread

Part no. S	Part no. M	Part no. SPR-AS	Part no. SPR-PVC-AS SPR-PU-AS	Part no. SPR-EDU-AS	Size PG	Tube outer Ø mm	Thread length mm	Unit	Net EUR/100 items at a purchase of		
									up to 100	101 - 500	501 - 1000
98322	98206	98215	98224	905997	7	10,0	7,0	50	o. r.	o. r.	o. r.
98323	98207	98216	98225	905998	9	14,0	7,0	50	o. r.	o. r.	o. r.
98324	98208	98217	98226	905999	11	17,0	7,0	50	o. r.	o. r.	o. r.
98325	98209	98218	98227	906000	13,5	19,0	7,0	50	o. r.	o. r.	o. r.
98326	98210	98219	98228	906001	16	21,0	7,0	50	o. r.	o. r.	o. r.
98327	98211	98220	98229	906002	21	27,0	10,0	25	o. r.	o. r.	o. r.
98328	98212	98221	98230	906003	29	36,0	10,0	25	o. r.	o. r.	o. r.
98329	98213	98222	98231	906004	36	45,0	10,0	20	o. r.	o. r.	o. r.
98330	98214	98223	98232	906005	48	56,0	10,0	10	o. r.	o. r.	o. r.

PG thread - small package

Part no. S	Part no. M	Part no. SPR-AS	Part no. SPR-PVC-AS SPR-PU-AS	Part no. SPR-EDU-AS	Size PG	Tube outer Ø mm	Thread length mm	Unit	Net EUR/100 items at a purchase of		
									up to 100	101 - 500	501 - 1000
93520		93560	93580		7	10,0	7,0	10	o. r.	o. r.	o. r.
93521		93561	93581		9	14,0	7,0	10	o. r.	o. r.	o. r.
93522		93562	93582		11	17,0	7,0	10	o. r.	o. r.	o. r.
93523		93563	93583		13,5	19,0	7,0	10	o. r.	o. r.	o. r.
93524		93564	93584		16	21,0	7,0	10	o. r.	o. r.	o. r.
93525		93565	93585		21	27,0	10,0	10	o. r.	o. r.	o. r.
93526		93566	93586		29	36,0	10,0	2	o. r.	o. r.	o. r.
93527		93567	93587		36	45,0	10,0	2	o. r.	o. r.	o. r.
93528		93568	93588		48	56,0	10,0	2	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request