

LI tube gland, metal

with retaining ring



LI
 Tube gland for protection tubes type S, S-PU, M, SPR-AS, SPR-EDU-AS, SPR-PVC-AS.
 The rotating interior sockets with tube rotation lock is inserted into the gland and secured against tearing by the spring steel ring.

Material
 Brass, nickel plated
 Grounding sleeve: Brass, bare
 Retaining ring: ex spring steel

Technical data
 Protection class: IP 40
 Temperature range: -40°C up to +250°C

metric thread

Part no.	Size	Tube outer Ø mm	Thread length mm	Unit	Net EUR/100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
97619	M10 x 1,0	10,0	10,0	50	o. r.	o. r.	o. r.
97620	M12 x 1,5	14,0	10,0	50	o. r.	o. r.	o. r.
97621	M16 x 1,5	17,0	10,0	50	o. r.	o. r.	o. r.
97622	M20 x 1,5	21,0	10,0	50	o. r.	o. r.	o. r.
97623	M25 x 1,5	27,0	11,0	25	o. r.	o. r.	o. r.
97624	M32 x 1,5	36,0	13,0	25	o. r.	o. r.	o. r.
97625	M40 x 1,5	45,0	13,0	25	o. r.	o. r.	o. r.
97626	M50 x 1,5	56,0	14,0	25	o. r.	o. r.	o. r.

metric thread - small packages

Part no.	Size	Tube outer Ø mm	Thread length mm	Unit	Net EUR/100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
93610	M10 x 1,0	10,0	10,0	10	o. r.	o. r.	o. r.
93611	M12 x 1,5	14,0	10,0	10	o. r.	o. r.	o. r.
93612	M16 x 1,5	17,0	10,0	10	o. r.	o. r.	o. r.
93613	M20 x 1,5	21,0	10,0	10	o. r.	o. r.	o. r.
93614	M25 x 1,5	27,0	11,0	10	o. r.	o. r.	o. r.
93615	M32 x 1,5	36,0	13,0	2	o. r.	o. r.	o. r.
93616	M40 x 1,5	45,0	13,0	2	o. r.	o. r.	o. r.
93617	M50 x 1,5	56,0	14,0	2	o. r.	o. r.	o. r.

Continuation ►

L tube gland, metal

with retaining ring

PG thread

Part no.	Size PG	Tube outer Ø mm	Thread length mm	Unit	Net EUR/ 100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
90730	7	10,0	7,0	50	o. r.	o. r.	o. r.
90731	9	14,0	7,0	50	o. r.	o. r.	o. r.
90732	11	17,0	7,0	50	o. r.	o. r.	o. r.
90733	13,5	19,0	7,0	50	o. r.	o. r.	o. r.
90734	16	21,0	7,0	50	o. r.	o. r.	o. r.
90735	21	27,0	10,0	25	o. r.	o. r.	o. r.
90736	29	36,0	10,0	25	o. r.	o. r.	o. r.
90737	36	45,0	10,0	25	o. r.	o. r.	o. r.
90738	48	56,0	10,0	10	o. r.	o. r.	o. r.

PG thread - small packages

Part no.	Size PG	Tube outer Ø mm	Thread length mm	Unit	Net EUR/ 100 items at a purchase of		
					up to 100	101 - 500	501 - 1000
93600	7	10,0	7,0	10	o. r.	o. r.	o. r.
93601	9	14,0	7,0	10	o. r.	o. r.	o. r.
93602	11	17,0	7,0	10	o. r.	o. r.	o. r.
93603	13,5	19,0	7,0	10	o. r.	o. r.	o. r.
93604	16	21,0	7,0	10	o. r.	o. r.	o. r.
93605	21	27,0	10,0	10	o. r.	o. r.	o. r.
93606	29	36,0	10,0	2	o. r.	o. r.	o. r.
93607	36	45,0	10,0	2	o. r.	o. r.	o. r.
93608	48	56,0	10,0	2	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request