



## EF

Universal applications.  
Protection tube from reinforced, galvanised steel band with spiral wound, latched profile, a continuous cord seal and extruded plastic sheath. This complex construction method keeps the plastic sheath and the internal tube flush together.

## Material

Galvanised steel

Outer sheath material: PVC

## Note

Suitable connection glands:  
LT straight, LT angled, T&B straight, T&B angled.  
Dimensions 2 1/2", 3", 4", 5" and 6" available on request.

## Technical data

Protection class: IP 67

Temperature range: -25°C up to +70°C  
Temperature range temporary up to +90°C

Part no. grey	Part no. black	Trade size inch	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/ 100 metres at a purchase of		
						up to 100	101 - 500	501 - 1000
91229	96939	1/4"	6,4	11,5	50	o. r.	o. r.	o. r.
91230	96248	5/16"	10,1	14,4	50	o. r.	o. r.	o. r.
91231	96249	3/8"	12,6	17,8	75	o. r.	o. r.	o. r.
91232	97153	1/2"	16,0	21,1	60	o. r.	o. r.	o. r.
91233	96718	3/4"	21,0	26,4	50	o. r.	o. r.	o. r.
91234	96250	1"	26,5	33,1	30	o. r.	o. r.	o. r.
91235	96251	1 1/4"	35,1	41,8	30	o. r.	o. r.	o. r.
91236	97175	1 1/2"	40,3	47,8	15	o. r.	o. r.	o. r.
91237	96252	2"	51,6	59,9	15	o. r.	o. r.	o. r.

## small package

Part no. grey	Part no. black	Trade size inch	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/ 100 metres at a purchase of		
						up to 100	101 - 500	501 - 1000
94915	94930	5/16"	10,1	14,4	10	o. r.	o. r.	o. r.
94916	94931	3/8"	12,6	17,8	10	o. r.	o. r.	o. r.
94917	94932	1/2"	16,0	21,1	10	o. r.	o. r.	o. r.
94918	94933	3/4"	21,0	26,4	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request