



Bulk Cables								
Cable	Characteristics and advantages	Area (mm ²)	Structure (strand mm)	Resistance (Ohm/km)	Capacity Conduct-conduct (pF)	Jacket	Colors	Diameter (mm)
intro cable 1	Microphone	0,22	28 x 0,1	80	80	PVC mat	black&white	5,9
intro cable 2	Microphone	0,22	28 x 0,1	80	80	PVC mat	black&white	4,3
intro cable 3	Twin Microphone	0,22	28 x 0,1	80	80	PVC mat	black&white	4,3
intro cable 4	Twin Microphone	0,22	28 x 0,1	80	90	PVC mat	black&white	4,6
intro cable 5	Guitar/Instrument	0,22	7 x 0,2	80	140	PVC mat	black	5,9
intro cable 6	Multicore	0,22	7 x 0,2	79	72	PVC mat	black	15
intro cable 7	Loudspeaker	1,5	48 x 0,2	12	200	PVC mat	black	7
intro cable 8	Loudspeaker	2,5	48 x 0,2	7	200	PVC mat	black	7,8
intro cable 9	DMX (Impedance 110 Ohm)	0,15	19 x 0,1	120	75	PVC mat	black	3,5