

# SPECIFICATIONS / TENDER

**Type** Microphone cable

**Part no.** CMK 222

## Mechanical data

Conductor area 0,22 mm<sup>2</sup>

Composition of conductor 28 x 0,10 mm bare copper

Conductor isolation PE

Composition of cores 2 twisted pairs

Screen spiral wound copper wire screen

Overall jacket PVC

Overall diameter 6,4 ± 0,2 mm

Weight<sup>53</sup> g/m

## Working temperature

mobile (-5 °C) - (+70 °C)

fixed (-20 °C) - (+70 °C)

**min.Bending radius**

mobile ~ 66 mm

fixed ~ 33 mm

### **Electrical data**

Conductor resistance <85  $\Omega$  / km

Capacity (cond./cond.) 55 pF / m

Capacity (cond./screen) 1110 pF / m

Test Voltage 750 V eff.

## **Product Variants**

Colour	Part number
black	CPM 1 FM
black	CPM 1.5 FM
black	CPM 2.5 FM
black	CPM 3 FM
black	CPM 5 FM

Colour	Part number
black	CPM 6 FM
black	CPM 7.5 FM
black	CPM 10 FM
black	CPM 15 FM
black	CPM 20 FM
purple	CPM 5 FM-BL
purple	CPM 10 FM-BL
red	CPM 5 FM-RT
red	CPM 10 FM-RT