


FILE NO.	Bestell No.	UNO ITEM NO.	LENGTH	Renkforce giftbox
29212c137	1650567	780160	150+50mm/-0mm	10.5*14cm(depth:3.0cm)

**MATERIAL LIST:**

⑪	FERRITE CORE	ID:7.6*11*20MM , OUTER MOLD PVC BLACK	1	
⑩	DUST CAP	LD-PE WHITE	1	
⑨	TUBE END	BLACK PVC	2	
⑧	THUMB SCREW	B-L30.5 BLACK PVC	2	
⑦	OUTER COVER	PVC BLACK	2	
⑥	HOUSING	ABS BLACK	1	
⑤	INNER COVER	LD PE	2	
④	CONNECTOR	MICRO USB 5P/F WITH SOLDER TYPE, BLACK INSULATION, THE PIN GOLD PLATED , THE SHELL FOR NICKEL PLATED	1	
③	CONNECTOR	DVI 24+1/M WITH SOLDER TYPE, BLACK INSULATION, THE PIN GOLD PLATED , THE SHELL FOR NICKEL PLATED	1	
②	CONNECTOR	VGA/F WITH SOLDER TYPE, BLUE INSULATION, THE PIN GOLD PLATED , THE SHELL FOR NICKEL PLATED , With IC	1	
①	CABEL	(32AWG TC*1P+D+FAM)*4+(32AWG TC) *4C+AL-FOIL+DRAIN WIRE+BRAID BLACK PVC JACKET, OD :4.8±0.2MM	1	



Label

**NOTE:**

- Electrical test:
  - 100% open short & miss wire test;
  - 1920\*1080@60HZ
  - operation temperature:-10°C ~ +60°C  
Storage temperature:-20°C ~ +75°C
  - RoHS2.0 ADN REACH COMPLIANT
  - Packing:VP1-2:105 x 140(depth:30mm), Including 2 sheets (4 pages) Renkforce 4 lang manual, A4
  - MARKING:High Speed HDMI™ Cable

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK	CUSTOMER	CN	ITEM NO.	1650567		
Alei	Alvan	change the distance of FERRITE to the end of the line to 50	2018.04.13	A1	PRODUCT NAME	DVI(24+1) male to VGA female	UNO ITEM NO.	780160	UNIT	MM
			2017.11.23	A	DRAWNBY	CHECKBY	APPOBY	DATE		
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	Alei	Alvan	2018.04.13			