



19" 4 Post Open Frame Rack

26U, Flatpacked, Black

Part No.: **714242**

Intellinet 4 Post Open Frame Racks provide a sturdy, low cost solution to support large rackmount equipment. Whether for servers, telecom equipment or other network facilities, the rack provides the strength and stability of an enclosure with easy access to the equipment and cabling.

Features:

- Ideal for all 19 in. rackmount applications
- Fast Installation
- Adjustable depth from 22 to 40 in. (55.88 to 101.6 cm)
- Option to use castors, Feet or to bolt to floor
- Ships flatpacked
- Three-Year Warranty

Specifications:

General

- 19 in.
- Height: 26U
- Color: Black RAL9005
- Depth adjustable 22 to 40 inches (in 1 inch increments)
- 2.0mm steel
- Static load maximum 1360kg

Dimensions

- 558.8 to 1023 (L) x 514.5 (W) x 1295.2 (H) [mm]

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- 22 to 40.28 (L) x 20.26 (W) x 50.99 (H) [in]

Package Contents

- Flatpacked Four-Post Open-Frame Rack
- Four castors
- Four adjustable supporting feet
- Sixteen Cable-management hooks
- Assembly bolts, washers and nuts
- Assembly instructions



