



Success Wireless Optical Mouse

USB, Three Buttons with Scroll Wheel, 1000 dpi, Green/Black

Part No.: **179393**

The Manhattan Success Wireless Optical Mouse combines modern design with advanced precision and performance. Its full-sized shape and three-button configuration provide direct access to essential commands with minimal wrist movement. A non-slip texture applied to critical surfaces helps provide a secure, comfortable grip. The remarkably small yet powerful USB micro receiver with 2.4GHz technology provides an effective range of up to 10 m (33 ft.) and stores in a special on-board compartment or remains installed for true wireless convenience.

Features:

- Precision optical performance in an agile, modern design with USB micro receiver
- 2.4GHz RF technology offers wireless freedom with effective range up to 10 m (33 ft.)
- Auto power management helps maintain proper battery levels
- On-board storage compartment protects USB receiver from loss and damage
- Ergonomic shape and no-slip texture provide secure grip
- Low-friction base smoothly glides over work surfaces
- Plug-and-play installation — Windows and Mac compatible
- Three-Year Warranty

Specifications:

Standards and Certifications

- USB
- CE
- FCC
- RoHS2
- WEEE

General

- Receiver (2.4 GHz)
- RF wireless range: up to 10.0 m (33 ft.)

- Mouse: optical sensor (A3000); 1000 dpi resolution
- Controls: right and left mouse with scroll wheel (auto-scroll)
- Automatic power save / power off mode
- Material: ABS plastic
- Compatible with Windows and Mac

Dimensions

- Mouse: 10 x 6 x 3.5 cm (4 x 2.4 x 1.4 in.); 50 g (1.8 oz.)
- USB micro receiver: 1.9 x 1.5 x 0.6 cm (0.8 x 0.5 x 0.3 in.)

Environmental

- Operational temperature: 0°C (32°F) – 45°C (113°F)
- Storage temperature: -15°C (5°F) – 60°C (140°F)
- Working humidity: <85%

Package Contents

- Success Wireless Optical Mouse with USB micro receiver
- 1 x AA battery
- Instructions



