



Curve Wireless Optical Mouse

USB, Five Button with Scroll Wheel, 1600 dpi, Blue/Black

Part No.: **179294**

The Manhattan Curve optical wireless mouse combines modern design with advanced precision and high-stabilization performance. Its top-mount push-button instantly shifts resolution from 800, 1200 and 1600 dpi to suit a wide range of applications, including routine computing tasks or computer games and editing requiring a fine touch. Its full-sized shape and five-button configuration provide direct access to essential commands with minimal wrist movement. A non-slip texture applied to critical surfaces helps provide a secure, comfortable grip. The remarkably small yet powerful USB micro receiver with 2.4GHz technology provides an effective range of up to 10 m (33 ft.) and stores in a special on-board compartment or remains installed for true wireless convenience. Automatic power management helps maintain proper battery levels for reliable operation. Plug-and-play capability and Windows and Mac OS compatibility offer quick and easy installation. The Curve wireless optical mouse requires little maintenance for long-term, dependable service.

Features:

- Precision optical performance in an agile, modern design with USB micro receiver
- 2.4GHz RF technology offers wireless freedom with effective range up to 10 m (33 ft.)
- Auto power management helps maintain proper battery levels
- On-board storage compartment protects USB receiver from loss and damage
- Top-mount push-button control instantly shifts resolution from 800, 1200 and 1600 dpi
- Ergonomic shape and no-slip texture provide secure grip
- Low-friction base smoothly glides over work surfaces
- Plug-and-play installation; Windows and Mac compatible
- Three-Year Warranty

Specifications:

Standards and Certifications

- USB
- CE

- FCC
- RoHS2
- WEEE

General

- Receiver (2.4 GHz)
- RF wireless range: up to 10.0 m (33 ft.)
- Mouse: optical sensor (A3000); 800/1200/1600 dpi resolution
- Controls: right and left mouse with scroll wheel (auto-scroll), page forward, page back, resolution adjustment
- Automatic power save / power off mode
- Material: ABS plastic
- Compatible with Windows and Mac

Dimensions

- Mouse: 10.9 x 7.5 x 3.8 cm (4.3 x 2.9 x 1.6 in.); 61.5 g (2.2 oz.)
- USB micro receiver: 1.9 x 1.5 x 0.6 cm (0.8 x 0.5 x 0.3 in.)

Environmental

- Operational temperature: 0°C (32°F) – 45°C (113°F)
- Storage temperature: -15°C (5°F) – 60°C (140°F)
- Working humidity: <85%

Package Contents

- Curve Wireless Optical Mouse with USB micro receiver
- 2 x AAA batteries
- Instructions



