



Edge Optical USB Mouse

USB, Wired, Three Buttons with Scroll Wheel, 1000 dpi, Blue
Part No.: [177801](#)

A practical design with stylish accents, full function and performance.

The Manhattan Edge Optical USB Mouse, with its 1000dpi resolution sensor, offers reliable performance. A modern design is highlighted by a stylish color panel. Its compact size and ambidextrous shape feature a familiar three-button design with scroll-wheel configuration ideal for daily computing needs.

Easy Installation and Low Maintenance

Plug-and-play installation and compatibility with Windows XP/Vista/7/8.1/10 offer quick and easy operation. With no mechanical or rolling parts to wear or fail, the Manhattan Edge Optical USB Mouse requires little maintenance to maintain reliable performance.

Features:

- Compact size, ergonomic and ambidextrous design offers comfortable grip with less fatigue
- Low-friction base smoothly glides over work surfaces
- Plug-and-play installation — Windows and Mac compatible
- Three-Year Warranty

Specifications:

Standards and Certifications

- USB
- CE
- FCC
- RoHS2
- WEEE

General

- USB interface
- Mouse: optical, 1000dpi resolution
- Controls: right and left mouse with scroll wheel buttons
- Material: ABS plastic
- Compatible with Windows XP/Vista/7/8.1/10 and Mac OS 9 and up

Dimensions

- Mouse: 10.9 x 6 x 4 cm (4.3 x 2.3 x 1.6 in.); 79g (2.8 oz.)
- USB cable: 1.5 m (4.9 ft.)

Environmental

- Operational temperature: 0 - 45°C (32 - 113°F)
- Storage temperature: -40 - 45°C (-40 - 113°F)
- Working humidity: < 85%
- Electrical: 5 V < 30 mA

Package Contents

- Edge Optical USB Mouse
- QIG



