

Distributed by Conrad Electronic SE • Klaus-Conrad-Str. 1 • D-92240 Hirschau

Datasheet

Item no. 1661346


V1 07262018 01 en


Horn Speaker, 20W, 88 x 102.5 x 104.2 mm

1.Specification

- 1.1 Coil Impedance: 8Ω
- 1.2 Input Power: 20W
- 1.3 Frequency Range:800-5K Hz
- 1.4 Operating Temperature Range:-20°C~+70°C
- 1.5 Storage Temperature Range: -20°C~+85°C
- 1.6 Material: ABS Plastic
- 1.7 Housing Color: Black
- 1.8 Net Weight: about 350g

3. Dimension





4.Product Photo



Test Voltage	Sound Pressure level
(AC)	(at 1K Hz, 1W/1M)
10 V	97 dB

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.