

Datasheet

Item no. 1661348


V1_07262018_01_en

Horn Speaker, 20W, 131 x 143x 142 mm

1. Specification

- 1.1 Coil Impedance: 8Ω
- 1.2 Input Power: 20W
- 1.3 Frequency Range: 700-5K Hz
- 1.4 Operating Temperature Range: -20°C~+70°C
- 1.5 Storage Temperature Range: -20°C~+85°C
- 1.6 Material: ABS Plastic
- 1.7 Housing Color: Black
- 1.8 Net Weight: about 500g

3. Dimension



4. Product Photo



Test Voltage (AC)	Sound Pressure level (at 1K Hz, 1W/1M)
10 V	102 dB