



# ***VOLTCRAFT***®

## **VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY**

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

## **6000 PB-60 LED POWER BANK**

**Nº 1661733**

**CE**

VERSION 05/18

The robust power bank is the ideal companion for outdoor activities and provides energy for mobile devices (e.g. smart-phone) even under adverse conditions. Due to its compact design and its light weight the power bank can be easily stored in a pocket or backpack. The built-in rechargeable battery can be charged via USB.

## **HIGHLIGHTS**

**LED light with 18 LEDs, 2 brightness settings, strobe light and SOS signal //**

**Li-ion rechargeable battery with 6000 mAh //**

**2 USB charging ports (max. 2.1 A total output) //**

**Protected against splash water (IP54) //**

**2 flexible suspension brackets //**

**Charging indicator //**



# TECHNICAL DATA

Input	5 V/DC, 2 A
Output	5 V/DC, max. 2.1 A (total)
Internal rechargeable battery	LiPo, 3.7 V, 6000 mAh
Number of LEDs	18
Charging duration	approx. 3.75 h via USB
Colour temperature	6000 – 6500 K
Protection type	IP54
Cable length	approx. 30 cm
Operating/storage temperature	0 to +45 °C
Dimensions (L x W x H)	150 x 77 x 15 mm
Weight	193 g

# PACKAGE CONTENT

Power bank // Micro-USB charger cable // Snap hook // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau ([www.conrad.com](http://www.conrad.com)).  
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.