

## 24" Full HD LED Monitor

Art.-Nr. TVAC10060

---



- 
- Resolution: 1920 x 1080 pixels
  - Fast reaction time (5 ms)
  - LED background lighting: brilliant colour display and contrast
  - Graphical on-screen display (OSD)
  - Connections: HDMI, DVI, VGA, audio input and output
  - Integrated loudspeakers
  - Low power consumption (LED technology)
  - For wall and ceiling installation (with VESA mount)
- 

The 24" LED monitor displays full HD 1080p pictures in 16:9 format, making it ideally suited for displaying megapixel surveillance pictures.

### Detailed surveillance pictures in full HD

Thanks to a rapid reaction time of just 5 ms, surveillance pictures in full HD are transmitted in a matter of seconds. Quick movements on the screen are shown clearly and continuously, without any distortions, flickering or ghost images. You see detailed, vivid pictures in full HD quality.

### Versatile connections

The connections ensure a high level of flexibility when connecting the monitor to a recorder or PC. Thanks to the HDMI connection, the monitor is optimally suited to displaying images in full HD. The VGA and DVI connections provide additional options, making the monitor a suitable component for versatile surveillance systems,

ABUS Security-Center



Security Tech Germany

## 24" Full HD LED Monitor

Art.-Nr. TVAC10060

---

and it is further equipped with an integrated loudspeaker and an audio input and output.

Energy efficiency

The efficient LED display ensures very low power consumption.

Easy installation

VESA standard mounts allow mounting to a wall or ceiling. This makes installation fast and easy.

## 24" Full HD LED Monitor

Art.-Nr. TVAC10060

Brightness	300 cd/m <sup>2</sup>
Color levels	16,7
Comb filter	3D
Connections	1 x HDMI, 1x DVI, 1 x VGA, 1 x PC Audio
Contrast ratio	1000:1
DC voltage supply	12 V
Dimensions	580 x 407 x 75 mm
Display surface	matte
Frequency range	30 – 80KHz (H) / 50 – 75Hz (V) GHz
Gross weight	5,2 kg
Height	425 mm
Horizontal/vertical viewing angle	160° x 160° °
Housing material	Plastic
Input	1 x HDMI, 1x DVI, 1 x VGA, 1 x PC Audio
Length	75 mm
Loudspeaker	2 x 1,5 W
Max. humidity	85 %
Max. operating temperature	50 °C
Min. operating temperature	0 °C
Monitor type	LED
Net weight	4 kg
Picture format	16:9

Pixel pitch	0.2715 x 0.2715 (H) x (V) mm
Power consumption	25 W
Power consumption	3.000 mA
Reaction time	5 ms
Scope of delivery 01 description	24" Full HD LED Monitor
Scope of delivery 01 quantity	1
Scope of delivery 02 description	Power supply
Scope of delivery 02 quantity	1
Scope of delivery 03 description	HDMI cable
Scope of delivery 03 quantity	1
Scope of delivery 04 description	VGA cable
Scope of delivery 04 quantity	1
Scope of delivery 05 description	PC Audio cable
Scope of delivery 05 quantity	1
Scope of delivery 06 description	Important safety information
Scope of delivery 06 quantity	1
Scope of delivery 07 description	Remote control
Scope of delivery 07 quantity	1

ABUS Security-Center



Security Tech Germany

## 24" Full HD LED Monitor

Art.-Nr. TVAC10060

---

Screen diagonal	23,6 "
Signal detection	Automatic
Width	580 mm