Motion Detector for 55mm frames - indoor

Product ref.: 151769A0



Technical specifications

Supply voltage	2x 1,5 V LR03/micro/AAA	
Current consumption	50 mA max.	
Battery life	2 years (typ.)	
Degree of protection	IP20	
Ambient temperature	5 to 35 °C	
Dimensions (W x H x D)	Without frame: 55 x 55 x 20 mm Including frame: 86 x 86 x 21.5 mm	
Weight	90 g (incl. batteries)	
Radio frequency band	868.0-868.6 MHz 869.4-869.65 MHz	
Typ. open area RF range	150 m	
Detection range	12 m	
Detection angle horizontal	80°	
Detection angle vertical	20°	











Product features

- Reliably detects movements as well as light intensity with an integrated brightness sensor
- Two push-buttons offer control of other Homematic IP devices, e.g for switching light sources on and off or for activating and deactivating the eco mode
- Ideal detection range of up to 12 m and detection angle of 80°
- When using the device in a Homematic IP security solution, supply voltage must be connected via the Homematic IP Power Supply Unit for brand switches (HmIP-BPS)
- Can be flexibly mounted with supplied adhesive strips or screws
- Easy to integrate into existing switches for 55 mm frames of leading manufacturers: Berker (S.1, B.1, B.3, B.7 Glas), GIRA (System 55, Standard 55, E2, E22, Event, Esprit), Merten (1-M, Atelier-M, M-Smart, M-Arc, M-Star, M-Plan), JUNG (A 500, AS 500, A plus, A creation), Busch Jaeger (balance® SI) and ELSO (Joy)
- Can be used with the Access Point in connection with the Homematic IP app (no recurring costs), the Homematic Central Control Unit CCU2 as well as with various partner solutions

Logistical data

Product reference	151769A0
EAN code	4047976517695
Short description	HmIP-SMI55
Packing unit	90
Packing dimensions	122 x 112 x 48 mm

Package contents

Homematic IP Motion Detector for 55mm frames – indoor	
Clip-on frame	
Mounting plate	
Mounting material (screws, plugs and adhesive strips)	
1.5 V LR03/micro/AAA batteries (2x)	

User manual