

FALCON 40

FOLDABLE, MULTI-VOLTAGE SOLAR PANEL

PANNEAU SOLAIRE PLIABLE MULTI TENSION | PANEL SOLAR PLEGABLE DE MULTIPLE VOLTAJE
PANNELLO SOLARE PIEGHEVOLE VOLTAGGIO MULTIPLIO | FALTBARES SOLARPANEL MIT MEHRFACHSPANNUNG

Lightweight, foldable solar panel for charging laptops & netbooks (<40W), tablets, smart phones, and other 5V & 20V devices with the power of the sun. Charges up to 3 devices simultaneously (2x USB, 1x DV). High-efficiency Monocrystalline cells from SunPower™ produce 25-35% more power compared to conventional cells. Weather-resistant thanks to its rugged, splash-proof design and high-wear fabric.

RECHARGES:

RECHARGE | RECARGA | RICARICA | LÄDT AUF



SPECIFICATIONS:

SPÉCIFICATIONS | ESPECIFICACIONES
SPECIFICAS | SPEZIFIKATIONEN

- 40W Foldable Solar Panel
- SunPower™ cells, high-efficiency monocrystalline
- 4x Metal eye-holes to attach solar panel to backpack
- Splash-proof (IPX4)
- Rugged polyester fabric
- 2x USB output: 5V /3A Max
- 1x DC output: 20V /1A
- LED indicator
- Weight: 910g
- Size: 290mm x 292 x 11mm (folded)
1200mm x 292mm x 3mm (unfolded)

KIT INCLUDES:

INCLUS DANS LE KIT | EL KIT INCLUYE
IL KIT INCLUDE | KIT BEINHÄLTET

- 40W Foldable Solar Panel
- 1x DC cable (2m)
- 1x USB-C to USB cable (1m)
- 1x Female USB-C to male Micro USB adapter
- 1x Laptop tips set (10 pieces)
- 1x 12V in car charging socket
- 2x Carabiners



 POWERTRAVELLER

CE FC IPX4

PART CODE: PTL-FLS040
EAN CODE: 5060 1769 8466 0