

DA-6100 OUTDOOR ANTENNA

Datasheet

Features

- Outdoor antenna with built-in LTE filter
- Water-proof and anti-UV housing
- Compact and Stylish design
- Different installation methods, wall-mounted or pole-mounted installation
- VHF / UHF reception
- Low noise amplifier technology



Technical specifications

Type:	Active
Frequency:	VHF 47-240 & UHF 470 – 790 MHz
Channels:	CH 21-60
Gain:	20 ± 3 dB
Return loss:	6 dB
Insertion loss:	< 2 dB
Impedance:	75 Ohm
LTE Filter attenuation:	793MHz 10dB 803MHz 24dB 820 MHz 57dB
Connector:	F-connector
Power supply:	12 V / 250 mA or 5V / 40mA from set-top-box

Dimensions and weight

Unit Size(WxDxH):	100 x 60 x 195 mm
Unit weight(Net):	0.5 Kg
Giftbox Size(WxDxH):	155 x 95 x 220 mm
Weight(Gross):	0.80 Kg
EAN number:	5706998028464
Item number:	18829
Shipping carton QTY:	12

Contents

- DA-6100 LTE antenna
- Fixing base
- Wall mounting package (plastic pole, screw)
- Pole Mounting kits (U type screws, butterfly type washer)
- Coaxial Cable (RF cable IEC male to IEC female 15 cm; IEC male to F male 3 m)
- Power inserter
- AC/DC Adaptor
- Operational Manual