

**A-series
AEP MC 2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	AEP MC 2.5
Order No.	2433820000
Version	A-series, End plate
GTIN (EAN)	4050118444278
Qty.	25 pc(s).

A-series
AEP MC 2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	1 mm	Width (inches)	0.039 inch
Height	106.8 mm	Height (inches)	4.205 inch
Depth	87.7 mm	Depth (inches)	3.453 inch
Net weight	7.1 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

Snap-on	Yes	With snap-in pegs	Yes
---------	-----	-------------------	-----

Classifications

ETIM 6.0	EC000886	eClass 6.2	27-14-11-33
eClass 9.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Engineering Data	STEP