

**ModuPlug
HDC XX5E01 MMSM12D-0100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Type	HDC XX5E01 MMSM12D-0100
Order No.	2451110100
Version	
GTIN (EAN)	4050118485660
Qty.	1 pc(s).

ModuPlug HDC XX5E01 MMSM12D-0100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.001 g
------------	---------

Temperatures

Limit temperature	-30 °C ... 90 °C
-------------------	------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Module side version	Male	Opposite side version	Male, straight, M12D
Cable length	1 m	Category	Cat. 5e
Coding	D	Contact surface	Au (Gold)
Insulation strength	$\geq 10^8 \Omega$	No. of poles	4
Plugging cycles	≥ 100	Pollution severity	2
Rated current	4 A	Rated voltage	250 V
Transmission rate	100 MBit/s	Type	Pin

Cable technical specifications

Cable length	1 m	Colour coding	white, yellow, blue, orange
Core cross-section	22 AWG	Halogen	No
Insulation	PE	Outside diameter	6.5 ± 0.2
Sheath material	PUR	Sheathing colour	green
Shielded	Yes		

Classifications

ETIM 6.0	EC002599	eClass 6.2	27-26-12-04
eClass 9.0	27-06-03-07	eClass 9.1	27-06-03-08

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN
--------------------	------------------------------------

ModuPlug HDC XX5E01 MMSM12D-0100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4