

WIL-860-W-M12G-0.3U-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The WIL-STANDARD: 24V DC LED lamp, only 8mm high, with very high light output (1315 lm) and long service life (greater than 10,000 h).

Extremely robust construction, solid encapsulation and metal housing - waterproof (IP67).

Its 6500K colour temperature (daylight) makes it suitable for a wide range of applications.

Very easy to connect thanks to M12 connector. Low current consumption means that a 24V, 0.5A DC power supply is sufficient for operation.

General ordering data

Type	WIL-860-W-M12G-0.3U-S
Order No.	2535910000
GTIN (EAN)	4050118547573
Qty.	1 pc(s).

WIL-860-W-M12G-0.3U-S
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	860 mm	Width (inches)	33.858 inch
Height	8 mm	Height (inches)	0.315 inch
Depth	40 mm	Depth (inches)	1.575 inch
Net weight	650 g		

Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-20 °C
Operating temperature	-20 - 60°C		

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	0.3 m		

Connection data

Version	pin, straight	Coding	A
Connection thread	M12	Tightening torque	0.8 Nm
Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)		

Electric data

Rated voltage (text)	24 V DC	Rated current	1,10 A
Power	32.5 W		

General technical data

Number of LEDs	168	Light colour (CCT)	6500K, White
Luminosity	3,470 cd	Light current	2,473 lm
Emitting angle	40 °	Illumination level	844 lux
Operating life	60.000 h	Type of mounting	Screw mounting
Drill hole spacing	845 mm	Impact resistance	IK05
Protection degree	IP67		

Material data

Housing main material	hard anodised aluminium	Encapsulation compound	PUR V0
Threaded ring material	PA	Material of end caps	Nickel-plated CuZn

Standards

Certificate no. (cULus)	E354496
-------------------------	---------

Classifications

ETIM 6.0	EC001959	eClass 6.2	27-11-06-31
eClass 9.0	27-11-06-40	eClass 9.1	27-11-06-40

Data sheet

WIL-860-W-M12G-0.3U-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data


[STEP](#)

WIL-860-W-M12G-0.3U-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing



L = 860mm L1 = 845mm