

**THM  
EL 15 MM RT 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

**Your benefits with MultiMark**

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Type               | EL 15 MM RT 30M                                       |
| Order No.          | <a href="#">2528270000</a>                            |
| Version            | THM, Device markers, 15, red                          |
| GTIN (EAN)         | 4050118538861                                         |
| Qty.               | 1 pc(s).                                              |
| compatible printer | <a href="#">2448870000</a> <a href="#">2430920000</a> |

**THM**  
**EL 15 MM RT 30M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |           |                 |              |
|------------|-----------|-----------------|--------------|
| Length     | 30,000 mm | Length (inches) | 1,181.1 inch |
| Height     | 15 mm     | Height (inches) | 0.591 inch   |
| Depth      | 0.1 mm    | Depth (inches)  | 0.004 inch   |
| Net weight | 133 g     |                 |              |

**General data**

|                           |                   |                             |                             |
|---------------------------|-------------------|-----------------------------|-----------------------------|
| Adhesive                  | Acrylate adhesive | Approval acc. to UL 969     | Yes                         |
| Colour                    | red               | Halogen                     | No                          |
| Length                    | 30,000 mm         | Material                    | Polyester                   |
| Number per roll           | 1                 | Operating temperature range | -40...120 °C                |
| UL 94 flammability rating | V-0               | Version                     | halogen-free, Self-adhesive |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC001288    | eClass 6.2 | 27-14-91-29 |
| eClass 9.0 | 27-40-06-29 | eClass 9.1 | 27-40-06-29 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                       |
|------------------|-----------------------|
| Engineering Data | <a href="#">EPLAN</a> |
|------------------|-----------------------|

**THM**  
**EL 15 MM RT 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

