

Product information

00 21 37

Tool Case "Robust45 Move" Electric

63 parts



- Extensively equipped with 63 brand tools, partly VDE-tested according to DIN EN 60900
- With a total of 147 inserting options
- Max. payload: 35 kg
- Volume: 45 litres
- For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle
- Gas pressure absorber in the hinge
- Pneumatically cushioned lid
- Extendable telescopic handle for comfortable transport
- Large smooth-running wheels
- Dimensions, exterior (W x H x D): 609 x 428 x 263 mm; dimensions, interior (W x H x D): 540 x 364 x 229 mm



General

Article No.	00 21 37
EAN	4003773082606
Weight	14,770 g
Dimensions	428 x 425 x 262 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	609 mm (540 mm)
Dimension exterior (interior) height mm	263 mm (229 mm)
Dimension exterior (interior) depth mm	428 mm (364 mm)

Content

08 26 145	1 x Needle-Nose Combination Pliers (145 mm) ⚡ 1000V  
12 52 195 SB	1 x KNIPEX PreciStrip16® Automatic Insulation Stripper (0,08 - 16 mm²)
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm²) ⚡ 1000V  
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) 
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool (180 mm) 
97 53 04	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 10 + 16 mm²)

Content	
	MM 
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (0,6 x 3,5 x 100 mm) ⚡ 1000V 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ1 x 80 mm) ⚡ 1000V 
98 52	1 x Cable Knife (190 mm) ⚡ 1000V
00 11 01	1 x Knipex KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems (92 mm)
26 26 200	1 x Knipex Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm) ⚡ 1000V   40° 
70 06 160	1 x Knipex Diagonal Cutter (160 mm) ⚡ 1000V 
74 06 200	1 x Knipex High Leverage Diagonal Cutter (200 mm) ⚡ 1000V 
87 01 180	1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (180 mm) 
0030312-0300	1 x Picard Locksmith's hammer (300 g)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
16135	1 x Stabila Spirit Level Type 70 Electric (430 mm)
18115	1 x Stabila Pocket Electric mini spirit level (68 mm)
003484	1 x Wera Kraftform Compact VDE 16 Slim ⚡ 1000V
003760	1 x Wera Joker open-end wrench (10 x 13 mm)
004018	1 x Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts (1/4")
Accessories	
00 21 37 LE	Tool Case "Robust45 Move" empty,

technical change and errors excepted



With document compartment

