

Product information

00 21 37 LE

Tool Case "Robust45 Move"

Empty



- With a total of 147 inserting options
- Max. payload: 35 kg
- Volume: 45 litres
- For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle

General

Article No.	00 21 37 LE
EAN	4003773082590
Weight	9,940 g
Dimensions	428 x 428 x 263 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	609 mm (540 mm)
Dimension exterior (interior) height mm	263 mm (229 mm)
Dimension exterior (interior) depth mm	428 mm (364 mm)

technical change and errors excepted



With document compartment



