

Product information

00 21 36 LE

Tool Case "Robust34"

Empty



- With a total of 93 inserting options
- Max. payload: 25 kg
- Volume: 34 litres
- For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle

General

Article No.	00 21 36 LE
EAN	4003773082576
Weight	7,100 g
Dimensions	419 x 419 x 215 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	510 mm (480 mm)
Dimension exterior (interior) height mm	215 mm (199 mm)
Dimension exterior (interior) depth mm	419 mm (356 mm)

technical change and errors excepted