

# KERN SW2000

Professionelles Schallpegelmessgerät der Premium-Klasse



## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	350 x 280 x 90 mm
Gross weight:	1,300 kg
Net weight:	700 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	300 x 80 x 36 mm

## Measuring system

Measuring range [Max]:	136 db
Readout [d]:	0,100 db
Weighing units:	dB

## Functions

Data hold function:	yes
Function to set limits:	yes
Peak function:	yes
Visual ready signal:	yes

## Environmental conditions

Maximum operating temperature:	50 °C
Minimum operating temperature:	-10 °C

## Power supply

Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	EURO

n/a: Mains adapter external

## Power supply

Operating time:	10 h
-----------------	------

## Category

Brand:	Sauter
Category:	Sound level meters
Product Group:	Sound level meter