

# KERN SU130.

Professionelles Schallpegelmessgerät, Klasse II

**KERN**<sup>®</sup>



## Measuring system

Measuring range [Max]:	130 db
Precision (of [Max]):	3 %
Readout [d]:	0,100 db
Weighing units:	dB

## Functions

Function to set limits:	yes
Peak function:	yes

## Environmental conditions

Maximum operating temperature:	40 °C
Minimum operating temperature:	-10 °C

## Category

Brand:	Sauter
Category:	Sound level meters
Product Group:	Sound level meter

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 210 x 53 mm
Gross weight:	770 g
Net weight:	170 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	236 x 63 x 26 mm